

**Thermocouple isolation minrale de style  
industriel avec tte de raccordement KNE - Type J  
- 6,0 mm de diamtre - 600 mm de longueur**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Vous avez besoin de calibrer votre capteur de température ?**

Traable selon les normes dtalonnage ISO17025 (UKAS), Labfacility offre un choix dtalonnage traable en 3 ou 5 points laide de notre installation dtalonnage interne, vous pouvez slectionner nimporte quel point de température entre -10C et +200C.

**Veillez noter que si vous ajoutez une option de calibrage votre commande, vous serez contact pour les informations de livraison.**

**Spfications****Specifications**

|                              |                                                                                    |
|------------------------------|------------------------------------------------------------------------------------|
| <b>Product Code</b>          | XE-3262-001                                                                        |
| <b>General Description</b>   | Highly flexible, sheath can be bent/formed to suit many applications and processes |
| <b>Sensor Type</b>           | Mineral insulated Thermocouple fitted with KNE terminal head                       |
| <b>Thermocouple Type</b>     | J                                                                                  |
| <b>Thermocouple Junction</b> | Insulated hot junction                                                             |
| <b>Probe Diameter</b>        | 6.0mm                                                                              |
| <b>Probe Length</b>          | 600mm                                                                              |
| <b>Sheath Material</b>       | 310 stainless steel sheath                                                         |
| <b>Head Type</b>             | KNE, Cast aluminium finish, screw type lid with chain                              |
| <b>Gland</b>                 | M16 x 1.5mm Plated brass gland fitted                                              |
| <b>Max. Temperature</b>      | 1100°C                                                                             |
| <b>Min. Temperature</b>      | -40°C                                                                              |
| <b>IP Rating</b>             | IP67                                                                               |