

**Thermocouple isolation minrale ANSI avec pot  
filet et 100 mm de plomb ANSI double torsad isol  
PFA - Type K - Gaine SS310 - 1,5 mm x 250 mm**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Vous avez besoin de calibrer votre capteur de température ?**

Traable selon les normes dtalonnage ISO17025 (UKAS), Labfacility offre un choix dtalonnage traable en 3 ou 5 points laide de notre installation dtalonnage interne.

**Veillez noter que si vous ajoutez une option de calibrage votre commande, vous serez contact pour les informations de livraison.**

**Spifications****Specifications**

|                              |                                                                                    |
|------------------------------|------------------------------------------------------------------------------------|
| <b>Product Code</b>          | XE-3059-001                                                                        |
| <b>General Description</b>   | Highly flexible, sheath can be bent/formed to suit many applications and processes |
| <b>Thermocouple Type</b>     | K                                                                                  |
| <b>Thermocouple Junction</b> | Insulated hot junction                                                             |
| <b>Probe Diameter</b>        | 1.5mm                                                                              |
| <b>Probe Length</b>          | 250mm                                                                              |
| <b>Sheath Material</b>       | 310 stainless steel                                                                |
| <b>Pot Type</b>              | M8 x 1.0mm fine pitch threaded pot seal (200°C)                                    |
| <b>Cable Length</b>          | 100mm                                                                              |
| <b>Cable Type</b>            | PFA twin twisted                                                                   |
| <b>Core / Strands</b>        | 7/0.2mm                                                                            |
| <b>Cable Termination</b>     | Bare tails                                                                         |
| <b>Max. Temperature</b>      | 1100°C                                                                             |
| <b>Standards Met</b>         | colour coded to ANSI MC96.1                                                        |