

**Thermocouple isolation minrale avec joint de pot  
uni et cble ANSI isol PFA - Type K avec longueur  
de cble de 1 m - 6,0 mm x 500 mm**

www.labfacility.co.uk  
01223 836000



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Vous avez besoin de calibrer votre capteur de température ?**

Traable selon les normes dtalonnage ISO17025 (UKAS), Labfacility offre un choix dtalonnage traable en 3 ou 5 points laide de notre installation dtalonnage interne.

**Veillez noter que si vous ajoutez une option de calibrage votre commande, vous serez contact pour les informations de livraison.**

**Spifications****Specifications**

|                              |                                                                                    |
|------------------------------|------------------------------------------------------------------------------------|
| <b>Product Code</b>          | XE-3036-001                                                                        |
| <b>General Description</b>   | Highly flexible, sheath can be bent/formed to suit many applications and processes |
| <b>Thermocouple Type</b>     | K                                                                                  |
| <b>Thermocouple Junction</b> | Insulated hot junction                                                             |
| <b>Probe Diameter</b>        | 6.0mm                                                                              |
| <b>Probe Length</b>          | 500mm                                                                              |
| <b>Sheath Material</b>       | 310 stainless steel sheath                                                         |
| <b>Pot Type</b>              | Plain pot seal (200°C)                                                             |
| <b>Cable Length</b>          | 1M                                                                                 |
| <b>Cable Type</b>            | PFA Teflon® insulated flat pair cable and tails (colour coded to ANSI MC96.1)      |
| <b>Core / Strands</b>        | 7/0.2mm                                                                            |
| <b>Cable Termination</b>     | Bare tails                                                                         |
| <b>Max. Temperature</b>      | 1100°C                                                                             |
| <b>Standards Met</b>         | colour coded to ANSI MC96.1                                                        |