




LABFACILITY


TEMPERATURE & PROCESS TECHNOLOGY

Dtecteurs film plat 500 ohms - Classe A - 2 mm x 5 mm



Labfacility are currently multi-sourcing flat film detectors in order to ensure we can maintain a supply service to our customers without affecting the quality or functionality for the foreseeable future.

All flat film detectors supplied, although differing in appearance and packaging in some cases, will meet the specifications as published on our data sheets.



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

LabFacility fournit actuellement plusieurs fois des dtecteurs film plat afin de garantir que nous pouvons maintenir un service dapprovisionnement nos clients sans affecter la qualit ou la fonctionnalit dans un avenir prvisible.

Tous les dtecteurs film plat fournis, bien que diffrant dans certains cas par leur apparence et leur emballage, rpondront aux spcifications publies dans nos fiches techniques.

Caractristiques techniques

Specifications

Product Code	XE-4630-001
Element/hot junction	Thin film construction
Element	Pt500 to IEC751
Max. Temperature	500°C
Min. Temperature	-50°C
Tolerance	Class A in accordance with IEC 60751
Dimensions	2mm Width x 5mm Length
Important Information	Resists vibration & shock