

**Thermocouple isolation minrale CEI avec joint en
pot ordinaire, 1 m de plomb IEC isol PFA et
terminaison de mini-prise - Type J - 1,0 mm x
1000 mm**

Image
Coming
Soon

Vous avez besoin de calibrer votre capteur de température ?

Traable selon les normes dtalonnage ISO17025 (UKAS), Labfacility offre un choix dtalonnage traable en 3 ou 5 points laide de notre installation dtalonnage interne.

Veillez noter que si vous ajoutez une option de calibrage votre commande, vous serez contact pour les informations de livraison.

Spcifications**Specifications**

Product Code	XE-0362-001
General Description	Plain pot seal (200°C) with 1 Metre of PFA insulated lead, 7/0.2mm flat pair with tails.
Sensor Type	Mineral Insulated
Thermocouple Type	J
Element/hot junction	Single element, junction insulated from sheath (offers protection against spurious electrical signals)
Probe Diameter	1.0mm
Probe Length	1000mm
Sheath Material	Stainless steel 321
Pot Type	Plain (+200°C)
Cable Length	1m
Cable Type	PFA Teflon® insulated flat pair cable and tails (colour coded to IEC 584)
Core / Strands	7/0.2mm
Termination Type	Fitted mini plug



Max. Temperature	+760°C
Min. Temperature	-100°C
Tolerance	Class 1
Standards Met	In accordance with IEC 584
Connector Type	Plug
Connector Size	Miniature
Colour	Black