



## Silicone Rubber Insulated Thermocouple Cable / Wire (IEC) Type K



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Good electrical and mechanical properties, highly flexible, resistant to oils, acids and other adverse fluids. Good heat resistance to 200°C although not suitable for direct use in high pressure steam applications.

### Specifications

## Specifications

<b>General Description</b>	Good electrical and mechanical properties, highly flexible, resistant to oils, acids and other adverse fluids. Good heat resistance to 200°C although not suitable for direct use in high pressure steam applications.
<b>Cable Length</b>	10m, 25m, 50m, 100m
<b>Core / Strands</b>	7/0.2mm
<b>Outer Colour</b>	Green
<b>+ Colour</b>	Green
<b>- Colour</b>	White
<b>Drain Wire</b>	No
<b>Insulation Material</b>	Silicone rubber insulated 7/0.2mm conductors, twisted together with silicone rubber outer jacket
<b>Max. Temperature</b>	+200°C
<b>Min. Temperature</b>	-40°C
<b>Screen</b>	No
<b>Standards Met</b>	Colour code (cores & jacket) to IEC-584-3
<b>Thermocouple Type</b>	K
<b>Tolerance</b>	Class 2 to IEC-584