



# LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

## **Thermocouple jonction expose IEC double torsade isol en PFA avec fiche miniature - Type T - Taille du brin 1/0,2 - Longueur 300 mm**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Jonction apparente soude réponse rapide, disponible dans la spécification de câble de classe 1 conformément à la norme BS EN 60584-3:2008 avec une terminaison de fiche miniature.

Ideal pour les applications de test et de développement.

### Specifications

## Specifications

|                     |                                                            |
|---------------------|------------------------------------------------------------|
| Product Code        | XE-0445-001                                                |
| General Description | Fast response, welded exposed junction                     |
| Sensor Type         | Exposed Junction                                           |
| Thermocouple Type   | T IEC                                                      |
| Cable Length        | 300mm                                                      |
| Cable Type          | Teflon® PFA insulated twin-twisted lead                    |
| Core / Strands      | 1/0.2mm                                                    |
| Termination Type    | Miniature flat pin plug colour coded in accordance IEC 584 |
| Max. Temperature    | 250°C                                                      |
| Min. Temperature    | -75°C                                                      |
| Tolerance           | Class 1                                                    |
| Standards Met       | IEC-584-3                                                  |
| Connector Type      | Plug                                                       |
| Connector Size      | Miniature                                                  |
| Series              | Exposed Junctions                                          |