


## **Thermocouple isol minral JIS avec joint simple et 1 m de plomb JIS isol en PFA - Type K - 1,5 mm x 250 mm**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Vous avez besoin d'atlonner votre capteur de temprature ?**

Traable selon les normes dtalonnage ISO17025 (UKAS), Labfacility propose le choix entre un talonnage traable en 3 ou 5 points via notre installation dtalonnage interne.

**Veillez noter que si vous ajoutez une option de calibration votre commande, vous serez contact pour les informations de livraison.**

**Caractristiques techniques****Specifications**

|                             |                                                                                                        |
|-----------------------------|--------------------------------------------------------------------------------------------------------|
| <b>Product Code</b>         | XE-2942-001                                                                                            |
| <b>General Description</b>  | Plain pot seal (200°C) with 1 Metre of PFA insulated lead, 7/0.2mm flat pair with tails.               |
| <b>Sensor Type</b>          | Mineral Insulated                                                                                      |
| <b>Thermocouple Type</b>    | K                                                                                                      |
| <b>Element/hot junction</b> | Single element, junction insulated from sheath (offers protection against spurious electrical signals) |
| <b>Probe Diameter</b>       | 1.5mm                                                                                                  |
| <b>Probe Length</b>         | 250mm                                                                                                  |
| <b>Sheath Material</b>      | 310 Stainless Steel                                                                                    |
| <b>Pot Type</b>             | Plain (+200°C)                                                                                         |
| <b>Cable Length</b>         | 1M                                                                                                     |
| <b>Cable Type</b>           | PFA Teflon® insulated flat pair cable and tails (colour coded to JIS)                                  |
| <b>Core / Strands</b>       | 7/0.2mm                                                                                                |
| <b>Termination Type</b>     | Bare Tails                                                                                             |



|                  |                   |
|------------------|-------------------|
| Max. Temperature | 1100°C            |
| Min. Temperature | -40°C             |
| Tolerance        | Class 1           |
| Standards Met    | JIS               |
| Series           | Mineral Insulated |